

ELASTECH

UFC160X46@12X60

EAN 4031582422313



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Elastech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	300 kg
Load capacity Static	600 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall weight	0.952 kg

WHEEL

Body material	Polyamide
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Precision ball bearing, stainless
Threadguards	With threadguard
Diameter	160 mm
Tread width	46 mm
Axle hole diameter	12 mm
Hub length	60 mm
Hardness of tread (A)	64 Shore A

HOUSING

Stainless	✓
-----------	---

ELASTECH

UFC160X46@12X60

EAN 4031582422313



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

