

PURETECH

PIP150x32-Ø8

EAN 4031582356694



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ○ ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Puretech
Tip	Tocak
Standard	EN12530 - Kastori uređaja
Nosivost na 3 km/h	80 kg
Električni provod	no
nerdjajući	no
Statički Nosivost	160 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0.43 kg

TOCAK

Tread hardness	mekan
Materijal za telo	polipropilen
materijal omotaca	Cvrsta guma, bez obeležavanja
Nošenje	precizini kuglicni lezaj
stitnici omotaca	Sa threadguard
Prečnik	150 mm
Širina omotac	32 mm
dimenzija rupa osovina	8 mm
dužina glavnice	36.5 mm
Teškoća gazećeg omotac (A)	75 Šor A

PURETECH

PIP150x32-Ø8

EAN 4031582356694

Broj porudžbine 00038560
Product Drawings



BETTER MOBILITY. BETTER LIFE.

