

AGILA STAINLESS

7470PJC100P30-13

EAN 4031582350456
Order number 00036337



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ● ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ● ● |

CORE ATTRIBUTES

| | |
|-----------------------------|---------------------------|
| Product name | Agila stainless |
| Type | Swivel castor |
| Standard | EN12530 - Devices Castors |
| Load capacity at 1.8 mph | 220.46 lb |
| Stainless | ✓ |
| Load capacity Static | 440.92 lb |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 140 °F |
| Overall height | 5.31 in |
| Overall width | 2.36 in |
| Overall weight | 1.23 lb |

WHEEL

| | |
|-----------------------|-----------------------------------|
| Body material | Polypropylene |
| Tread material | Thermoplastic rubber |
| Bearing | Precision ball bearing, stainless |
| Wheel color | Silver gray (RAL7001) |
| Threadguards | With threadguard |
| Diameter | 3.94 in |
| Tread width | 1.26 in |
| Body width | 1.26 in |
| Hardness of tread (A) | 87 Shore A |

HOUSING

| | |
|---------------------|-------------------------|
| Material | Stainless steel, medium |
| Fork shape | Broad |
| Swivel bearing | Two ball races |
| Color | Stainless steel |
| Offset | 1.5 in |
| Swivel radius | 3.46 in |
| Swivel interference | 6.93 in |
| Dome diameter | 2.36 in |

FITTING

| | |
|--------------------|--|
| Fitting type | Bolt hole |
| Bolt hole diameter | 0.51 in |
| Hint | Castors can be mounted with standard screws of any length. |

AGILA STAINLESS

7470PJC100P30-13

EAN 4031582350456
Order number 00036337



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

