

PRODUCT INFORMATION

ELASTECH

IEP300x60-Ø30 TFR

EAN 4031582428483



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL


Tread hardness	soft
Body material	Aluminum
Tread material	Elastic tire, black, vulcanized
Bearing	Precision ball bearing
Threadguards	Without threadguard
Diameter	11.81 in
Tread width	2.36 in
Axle hole diameter	1.18 in
Hub length	2.36 in
Hardness of tread (A)	67 Shore A

PERFORMANCE

Roll Performance	● ● ● ● ○ ○
Movement noise	● ● ● ● ○ ○
Attrition	● ● ● ● ○ ○
Corrosion resistance	● ● ● ● ○ ○

CORE ATTRIBUTES

Product name	Elastech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	1322.77 lb
Load capacity at 3.7 mph	1058.22 lb
Electric conductive	no
Stainless	no
Load capacity Static	2645.54 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	8.52 lb




PRODUCT INFORMATION

ELASTECH

IEP300x60-Ø30 TFR

EAN 4031582428483



BETTER MOBILITY. BETTER LIFE.