

LINEA SAFETY

592DUAP075L51-10 7001/7015

EAN 4031582378269

Broj porudžbine 00771095



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja ●●○○○

Buka u pokretu ●●●○○

Ishrana ●●●○○

otpornost na rdju ●●●○○

OSNOVNI ATRIBUTI

Naziv proizvoda	Linea safety
Tip kućišta	Sistem automatskog zaključavanja
Standard	EN12528 - tockovi za nameštaj
Nosivost na 3 km/h	100 kg
Statički Nosivost	200 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Sveukupna visina	75,5 mm
Ukupna širina	55 mm
Ukupna težina	0,186 kg

TOCAK

Materijal za telo	poliamid
materijal omotaca	Poliuretan, liveno
Nošenje	precizini kuglicni lezaj
Boja omotac	Slat siva (RAL7015)
Boja Tockak	Slat siva (RAL7015)
štيتnici omotaca	Sa threadguard
Prečnik	75 mm
Širina omotac	15 mm
dimenzija rupa osovina	0 mm
duzina glavčine	0 mm
Širina tela	15 mm
Teškoća gazećeg omotac (A)	92 Šor A

KUCISTE

Materijal	poliamid
oblik viljuska	kuciste za dva Tockak
okretni lezaj	stablo , okretanje
Boja	Srebrna siva (RAL7001)
ofset	23 mm
okretni radijus	65 mm
Otpor okretanju	130 mm
Prečnik kupole	30 mm
Savet	Sila da oslobodi 23 N i prolećni udar dužine 8 mm.

PRILAGOĐAVANJE

Tip uklapanja	zatvorena rupa za postavljanje B10
dimenzija rupa sraf	10 mm

Deutscher
dizajner
ClubInterzum
nagradaIF nagrada za
Dizajn

LINEA SAFETY

592DUAP075L51-10 7001/7015

EAN 4031582378269
Broj porudžbine 00771095



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

