

# ZETA REVERSE

468SITP250P63 180° SH80

EAN 4031582414486



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Zeta reverse
Housing type	Swivel castor with spring loaded directional lock
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	1763.7 lb
Load capacity at 3.7 mph	1410.96 lb
Load capacity Static	3527.39 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	140 °F
Overall height	11.42 in
Overall weight	9.76 lb

## WHEEL

Body material	Aluminum
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	9.84 in
Tread width	1.97 in
Hardness of tread (A)	80 Shore A

## HOUSING

Material	Steel sheet, very heavy
Fork shape	Broad, reinforced
Swivel bearing	Two ball races, reinforced or stainless
Offset	2.17 in
Swivel radius	6.1 in
Swivel interference	14.17 in

## FITTING

Fitting type	Rectangular plate
Plate length	5.39 in
Plate width	4.13 in
Plate hole length (Maximum)	4.13 in
Plate hole width (Minimum)	2.95 in
Plate hole width (Maximum)	3.15 in
Plate hole diameter	0.43 in

# ZETA REVERSE

468SITP250P63 180° SH80

EAN 4031582414486



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

