PRODUCT INFORMATION

MAXTECH

UAD 100x32-Ø12 HL44 natural/3004

EAN 4031582322750



Image may differ from the original product

WHEEL

Body material	Polyamide
Tread Material Mix	Polyurethane, injected
Bearing	Roller bearing, stainless
Wheel Color	Natural white
Diameter	100 mm
Tread width	32 mm
Axle Hole Diameter	12 mm
Hub Length	44 mm
Body width	32 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●○○
Attrition	●●●●○
Corrosion Resistance	●●●●●

CORE ATTRIBUTES

Product Name	Maxtech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	150 kg
Electric Conductive	No
Stainless	Yes
Load capacity Static	300 kg
Temperature range (Minimum)	-25 °C
Temperature range (Maximum)	80 °C
Overall weight	0.23 kg

© Copyright 2026 TENTE International GmbH


MAXTECH

UAD 100x32-Ø12 HL44 natural/3004

EAN 4031582322750

Order number 00034134

Product Drawings



© Copyright 2026 TENTE International GmbH