

# ALPHA

3478DIR100P62

EAN 4031582306262  
Order number 00006946



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Alpha
Type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	70 kg
Load capacity Static	140 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	128 mm
Overall weight	0.602 kg

## WHEEL

Body material	Sheet Steel
Tread material	Solid rubber, non-marking
Bearing	Roller bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	100 mm
Tread width	30 mm
Hardness of tread (A)	80 Shore A

## HOUSING

Material fork	Steel sheet, heavy
Fork shape	Broad

## FITTING

Fitting type	Small rectangular plate
Plate length	103 mm
Plate width	85 mm
Plate hole length (Minimum)	77 mm
Plate hole length (Maximum)	80 mm
Plate hole width (Maximum)	60 mm
Plate hole diameter	9 mm

# ALPHA

3478DIR100P62

EAN 4031582306262  
Order number 00006946



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

