

STEM

S70-8x25 / 10

EAN 4031582424669



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

FITTING

Fitting type	Threaded stem with hexagon neck, top
Stem diameter	8 mm
Stem length	25 mm

PERFORMANCE

Corrosion Resistance	● ● ● ○ ○
----------------------	-----------

CORE ATTRIBUTES

Product Name	Stem
Type	Accessory
Load capacity at 3 km/h	50 kg
Electric Conductive	No
Stainless	No
Load capacity Static	100 kg
Overall Height	6 mm
Overall weight	0.03 kg