

# AGILA CARE US

2444UAP150R26-28S

EAN 4031582387445



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                                                       |
|-----------------------------|-------------------------------------------------------|
| Product name                | Agila care US                                         |
| Housing type                | Swivel castor with central, total or directional lock |
| Standard                    | similar EN12531- Hospital Bed Castors                 |
| Load capacity at 1.8 mph    | 330.69 lb                                             |
| Load capacity at 2.5 mph    | 330.69 lb                                             |
| Load capacity Static        | 661.39 lb                                             |
| Temperature range (Minimum) | -40 °F                                                |
| Temperature range (Maximum) | 176 °F                                                |
| Overall height              | 7.6 in                                                |

## WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Polyamide              |
| Tread material        | Polyurethane, injected |
| Bearing               | Precision ball bearing |
| Threadguards          | With threadguard       |
| Diameter              | 5.91 in                |
| Tread width           | 1.26 in                |
| Hardness of tread (D) | 40 Shore D             |

## HOUSING

|                     |                        |
|---------------------|------------------------|
| Material            | Steel sheet, medium    |
| Fork shape          | Broad                  |
| Swivel bearing      | Precision ball bearing |
| Offset              | 1.97 in                |
| Swivel radius       | 4.92 in                |
| Swivel interference | 9.84 in                |

## FITTING

|               |                                     |
|---------------|-------------------------------------|
| Fitting type  | Stem with cam hole for profile bars |
| Bolt diameter | 1.1 in                              |
| Bolt length   | 3.78 in                             |

# AGILA CARE US

EAN 4031582387445

