

# DURATECH

U00050X20-Ø8 NATUR

EAN 4031582447699



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	50 mm
Tread width	20 mm
Axle hole diameter	8 mm
Hub length	21.7 mm
Hardness of tread (D)	75 Shore D

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Duratech
Housing type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	55 kg
Load capacity Static	110 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall weight	0.018 kg

# DURATECH

U00050X20-Ø8 NATUR

EAN 4031582447699



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

