

FOOTMASTER

FOOT MASTER GATD-075-ASF-HUD

EAN 4031582495232
Order number 00800112



BETTER MOBILITY. BETTER LIFE.




Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ○ ○ ○ ○ ○ |
| Movement noise | ○ ○ ○ ○ ○ |
| Attrition | ○ ○ ○ ○ ○ |
| Corrosion resistance | ○ ○ ○ ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---------------|
| Product name | Footmaster |
| Type | Swivel castor |
| Load capacity at 1.8 mph | 551.16 lb |
| Temperature range (Minimum) | 14 °F |
| Temperature range (Maximum) | 194 °F |
| Overall height | 4.84 in |
| Overall width | 5.16 in |
| Overall weight | 12.26 lb |

WHEEL

| | |
|-------------|----------------|
| Bearing | Unmachined hub |
| Diameter | 2.95 in |
| Tread width | 1.18 in |
| Body width | 1.18 in |

HOUSING

| | |
|---------------------|---------|
| Offset | 1.18 in |
| Swivel radius | 3.19 in |
| Swivel interference | 6.38 in |
| Dome diameter | 4.09 in |

FITTING

| | |
|-----------------------------|---------|
| Plate length | 4.41 in |
| Plate width | 4.41 in |
| Plate hole length (Maximum) | 3.62 in |
| Plate hole width (Maximum) | 3.62 in |
| Plate hole diameter | 0.35 in |

FOOTMASTER

FOOT MASTER GATD-075-ASF-HUD

EAN 4031582495232
Order number 00800112



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

