

LUMINA

A520Y0I050B10-11X20/10DOM38 9011

EAN 4031582340563
Order number 00071196



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---------------------------------|
| Product name | Lumina |
| Type | Swivel castor |
| Standard | EN12529 - Swivel Chairs Castors |
| Load capacity at 3 km/h | 40 kg |
| Electric conductive | ✓ |
| Load capacity Static | 80 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 60 °C |
| Overall height | 61 mm |
| Overall width | 55 mm |
| Overall weight | 0.1 kg |

WHEEL

| | |
|-----------------------|------------------------------------|
| Body material | Polypropylene, electric conductive |
| Tread material | Identical with wheel body |
| Bearing | Plain bearing with spacer tube |
| Axle | Riveted |
| Tread color | Graphite black (RAL9011) |
| Wheel color | Graphite black (RAL9011) |
| Threadguards | Without threadguard |
| Diameter | 50 mm |
| Tread width | 8 mm |
| Axle hole diameter | 0 mm |
| Hub length | 0 mm |
| Body width | 8 mm |
| Hardness of tread (D) | 65 Shore D |

HOUSING

| | |
|---------------------|---------------------------------------|
| Material fork | Polypropylene |
| Fork shape | Twin wheel housing, closed, with dome |
| Swivel bearing | Stem, swiveling |
| Colour | Graphite black (RAL9011) |
| Offset | 20 mm |
| Swivel radius | 52 mm |
| Swivel interference | 104 mm |
| Dome diameter | 38 mm |

FITTING

| | |
|---------------|----------------------------------|
| Fitting type | Stem with grip ring, with collar |
| Stem diameter | 11 mm |
| Stem length | 20 mm |

PRODUCT INFORMATION

LUMINA

A520YOI050B10-11X20/10DOM38 9011

EAN 4031582340563
Order number 00071196



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

