

# MAXTECH

PNR260x82-Ø20 HL74 yellow

EAN 4031582438185



BETTER MOBILITY. BETTER LIFE.

## PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Maxtech
Type	Wheel
Load capacity at 1.8 mph	165.35 lb
Electric conductive	no
Stainless	no
Load capacity Static	330.69 lb
Overall weight	4.3 lb

## WHEEL

Body material	Polypropylene
Tread material	Polyurethane, foamed
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	10.24 in
Tread width	3.23 in
Axle hole diameter	0.79 in
Hub length	2.91 in

# MAXTECH

PNR260x82-Ø20 HL74 yellow

EAN 4031582438185



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

