

PRODUCT INFORMATION

MAXTECH

PNR260x82-Ø20 HL74 yellow

EAN 4031582438185



BETTER MOBILITY. BETTER LIFE.

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Maxtech
Type	Wheel
Load capacity at 1.8 mph	165.35 lb
Electric conductive	no
Stainless	no
Load capacity Static	330.69 lb
Overall weight	4.3 lb

WHEEL

Body material	Polypropylene
Tread material	Polyurethane, foamed
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	10.24 in
Tread width	3.23 in
Axle hole diameter	0.79 in
Hub length	2.91 in

MAXTECH

PNR260x82-Ø20 HL74 yellow

EAN 4031582438185



BETTER MOBILITY. BETTER LIFE.

Product Drawings

