

DURATECH

UOR 125X40-Ø12 HL48,4

EAN 4031582323559
Order number 00030967



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Roller bearing
Wheel color	Natural white
Threadguards	Without threadguard
Diameter	4.92 in
Tread width	1.57 in
Axle hole diameter	0.47 in
Hub length	1.91 in
Body width	1.57 in
Hardness of tread (D)	75 Shore D

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Duratech
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	661.39 lb
Load capacity Static	1322.77 lb
Temperature range (Minimum)	-13 °F
Temperature range (Maximum)	176 °F
Overall weight	0.6 lb

DURATECH

UOR 125X40-Ø12 HL48,4

EAN 4031582323559
Order number 00030967



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

