

AGILA

2478PJO150P50

EAN 4031582302394
Order number 00029492



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ● ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---------------------------|
| Product name | Agila |
| Type | Fixed castor |
| Standard | EN12530 - Devices Castors |
| Load capacity at 3 km/h | 100 kg |
| Load capacity Static | 200 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 60 °C |
| Overall height | 185 mm |
| Overall width | 60 mm |
| Overall weight | 0.69 kg |

WHEEL

| | |
|-----------------------|-----------------------|
| Body material | Polypropylene |
| Tread material | Thermoplastic rubber |
| Bearing | Plain bearing |
| Wheel color | Silver grey (RAL7001) |
| Threadguards | Without threadguard |
| Diameter | 150 mm |
| Tread width | 32 mm |
| Body width | 32 mm |
| Hardness of tread (A) | 87 Shore A |

HOUSING

| | |
|---------------|---------------------|
| Material fork | Steel sheet, medium |
| Fork shape | Broad |
| Colour | Blue passivated |
| Dome diameter | 60 mm |

FITTING

| | |
|-----------------------------|-------------------|
| Fitting type | Rectangular plate |
| Plate length | 77 mm |
| Plate width | 67 mm |
| Plate hole length (Minimum) | 46.5 mm |
| Plate hole length (Maximum) | 51.5 mm |
| Plate hole width (Minimum) | 56 mm |
| Plate hole width (Maximum) | 61.5 mm |
| Plate hole diameter | 8.5 mm |

AGILA

2478PJO150P50

EAN 4031582302394
Order number 00029492



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

