

MAXTECH

UAK 050X20-Ø6,1

EAN 4031582322835
Broj porudžbine 00008698

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja ● ● ● ○ ○

Buka u pokretu ● ● ● ○ ○

Ishrana ● ● ● ○ ○

otpornost na rdju ● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Maxtech
Standard	EN12530 - Kastori uređaja
Nosivost na 3 km/h	50 kg
Statički Nosivost	100 kg
Temperaturni opseg (Minimalno)	-25 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	0,066 kg

TOCAK

Materijal za telo	poliamid
materijal omotaca	Poliuretan, liveno
Nošenje	konusi lezaj
Boja Tocak	Srebrna siva (RAL7001)
stitnici omotaca	Sa threadguard
Prečnik	50 mm
Širina omotac	20 mm
dimenzija rupa osovina	6 mm
dužina glavcine	22 mm
Širina tela	20 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D

MAXTECH

UAK 050X20-Ø6,1

EAN 4031582322835
Broj porudžbine 00008698



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

