

R07-Ø19-21,5 INOX

EAN 4031582428261



Image may differ from the original product

PERFORMANCE

Corrosion resistance ● ● ● ○ ○

CORE ATTRIBUTES

|                             |           |
|-----------------------------|-----------|
| Product name                | Accessory |
| Housing type                | Accessory |
| Temperature range (Minimum) | 14 °F     |
| Temperature range (Maximum) | 104 °F    |
| Overall weight              | 0.26 lb   |

FITTING

|                            |  |
|----------------------------|--|
| Fitting type               | Synthetic expander, round                                  |
| Expander fitting (Minimum) | 0.75 in  |
| Expander fitting (Maximum) | 0.85 in  |
| Hint                       | Please indicate required tube innerdiameter when ordering. |