

# GALEA

5071PJH125P30-12

EAN 4031582378900



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                                     |
|-----------------------------|-------------------------------------|
| Product name                | Galea                               |
| Type                        | Swivel castor with directional lock |
| Standard                    | EN12530 - Devices Castors           |
| Load capacity at 3 km/h     | 100 kg                              |
| Load capacity Static        | 200 kg                              |
| Temperature range (Minimum) | -20 °C                              |
| Temperature range (Maximum) | 60 °C                               |
| Overall height              | 162 mm                              |
| Overall width               | 66 mm                               |
| Overall weight              | 0.541 kg                            |

## WHEEL

|                       |                      |
|-----------------------|----------------------|
| Body material         | Polypropylene        |
| Tread material        | Thermoplastic rubber |
| Bearing               | Plain bearing        |
| Threadguards          | With threadguard     |
| Diameter              | 125 mm               |
| Tread width           | 30 mm                |
| Hardness of tread (A) | 87 Shore A           |

## HOUSING

|                     |                |
|---------------------|----------------|
| Material fork       | Polyamide      |
| Fork shape          | Closed         |
| Swivel bearing      | Two ball races |
| Offset              | 40 mm          |
| Swivel radius       | 129 mm         |
| Swivel interference | 258 mm         |
| Dome diameter       | 59 mm          |

## FITTING

|                    |           |
|--------------------|-----------|
| Fitting type       | Bolt hole |
| Bolt hole diameter | 12 mm     |

# GALEA

5071PJH125P30-12

EAN 4031582378900



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

