

DURATECH SILENT

UOT 100x36-Ø8,4 HL45

EAN 4031582338041



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Duratech silent
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	551.16 lb
Electric conductive	no
Stainless	no
Load capacity Static	1102.31 lb
Temperature range (Minimum)	-22 °F
Temperature range (Maximum)	176 °F
Overall weight	0.67 lb

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Precision ball bearing, damped
Wheel color	Natural white
Diameter	3.94 in
Tread width	1.42 in
Axle hole diameter	0.33 in
Hub length	1.77 in
Body width	1.42 in
Hardness of tread (D)	75 Shore D

DURATECH SILENT

UOT 100x36-Ø8,4 HL45

EAN 4031582338041

Order number 00033627

Product Drawings



BETTER MOBILITY. BETTER LIFE.

