

# ELASTECH

XLP125X40-Ø8,3 HL45 ESD



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polyamide, electric conductive
	soft
Tread material	Elastic tire, non-marking, antistatic, vulcanized
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	4.92 in
Tread width	1.57 in
Hardness of tread (A)	64 Shore A

## PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Elastech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	352.74 lb
Electric conductive	✓
Load capacity Static	705.48 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	176 °F
Overall weight	1.43 lb

# ELASTECH

XLP125X40-Ø8,3 HL45 ESD



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

XLP125x40-Ø8,3 NL45

