

# NOVATECH

FTP 150X50-Ø25 HL60

EAN 4031582329476

Broj porudžbine 00802328



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOCAK

Materijal za telo	Ливено Гвожђе
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj
Boja Tocak	Med žuta (RAL1005)
stitnici omotaca	Sa threadguard
Prečnik	150 mm
Širina omotac	50 mm
dimenzija rupa osovina	25 mm
dužina glavcine	60 mm
Širina tela	50 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D

## PERFORMANSE

Performanse kotrljanja ●●●●○

Buka u pokretu ●●●○○

Ishrana ●●●●○

otpornost na rdju ●●●○○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Tip	Tocak
Standard	EN12533 - Tockoviza teske terete
Nosivost na 4 km/h	840 kg
Nosivost na 6 km/h	700 kg
Statički Nosivost	1400 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	3,564 kg

# NOVATECH

FTP 150X50-Ø25 HL60

EAN 4031582329476

Broj porudžbine 00802328



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

