


NOVATECH

RK.ETP080X62-Ø47X18

EAN 4031582369526
Broj porudžbine 00832666

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	Nedefinisani
materijal omotaca	polipropilen, mekan
Prečnik	80 mm
Širina omotac	62 mm
Teškoća gazećeg omotac (A)	92 Šor A
Prečnik kuglicni lezaj	47 mm
Širina kuglicni lezaj	18 mm

PERFORMANSE

Performanse kotrljanja	● ● ● ● ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Tip	Tocak
Nosivost na 3 km/h	600 kg
Statički Nosivost	1200 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C

TEHNIČKI CRTEŽI

