

# ULTRATECH PLUS

FCP200X50-Ø20 PLUS

EAN 4031582445206



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

|                       |                                |
|-----------------------|--------------------------------|
| Body material         | Casting                        |
| Tread material        | Ultratech Polyurethane, casted |
| Bearing               | Precision ball bearing         |
| Threadguards          | With threadguard               |
| Diameter              | 7.87 in                        |
| Tread width           | 1.97 in                        |
| Axle hole diameter    | 0.79 in                        |
| Hub length            | 2.36 in                        |
| Hardness of tread (A) | 92 Shore A                     |

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ● ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Ultratech plus                |
| Type                        | Wheel                         |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph    | 1763.7 lb                     |
| Load capacity at 3.7 mph    | 1410.96 lb                    |
| Load capacity Static        | 3527.39 lb                    |
| Temperature range (Minimum) | -4 °F                         |
| Temperature range (Maximum) | 140 °F                        |
| Overall weight              | 2.87 lb                       |

# ULTRATECH PLUS

FCP200X50-Ø20 PLUS

EAN 4031582445206



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

