

AGILA CARE US

2440UAP200R05-32

EAN 4031582387346



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila care US
Housing type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	150 kg
Load capacity Static	300 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall height	240 mm

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	200 mm
Tread width	32 mm
Hardness of tread (D)	40 Shore D

HOUSING

Material fork	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Precision ball bearing
Offset	62 mm
Swivel radius	162 mm
Swivel interference	324 mm

FITTING

Fitting type	Solid stem, round
Bolt diameter	32 mm
Bolt length	50 mm

AGILA CARE US

2440UAP200R05-32

EAN 4031582387346



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

