

PURETECH AIR

DQP260x85-Ø20 HL74 6PR

EAN 4031582428858



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Tread hardness	soft
Body material	Sheet Steel
Tread Material Mix	Pneumatic tyre, block profile
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	260 mm
Tread width	85 mm
Axle Hole Diameter	20 mm
Hub Length	74 mm
Hardness of tread (A)	55 Shore A

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Puretech air
Type	Wheel
Load capacity at 3 km/h	150 kg
Electric Conductive	No
Stainless	No
Load capacity Static	300 kg
Overall weight	1.57 kg

PURETECH AIR

DQP260x85-Ø20 HL74 6PR

EAN 4031582428858



BETTER MOBILITY. BETTER LIFE.

Product Drawings

