

# LINEA LIGHT

5925UAP100L51-11 7001/3000/7015

EAN 4031582350562



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |             |
|----------------------|-------------|
| Roll Performance     | ● ● ● ● ○ ○ |
| Movement Noise       | ● ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ ○ |
| Corrosion Resistance | ● ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                                |
|-----------------------------|--------------------------------|
| Product Name                | Linea light                    |
| Type                        | Swivel castor with wheel brake |
| Standard                    | EN12528 - Furniture Castors    |
| Load capacity at 3 km/h     | 100 kg                         |
| Electric Conductive         | No                             |
| Stainless                   | No                             |
| Load capacity Static        | 200 kg                         |
| Temperature range (Minimum) | -10 °C                         |
| Temperature range (Maximum) | 40 °C                          |
| Overall Height              | 100 mm                         |
| Overall width               | 73 mm                          |
| Overall weight              | 0.44 kg                        |

## HOUSING

|                     |                       |
|---------------------|-----------------------|
| Housing Material    | Polyamide             |
| Fork shape          | Twin wheel housing    |
| Swivel Bearing      | Stem, swiveling       |
| Housing Color       | Silver grey (RAL7001) |
| Offset              | 32 mm                 |
| Swivel radius       | 102 mm                |
| Swivel interference | 204 mm                |
| Dome diameter       | 41 mm                 |

## WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Polyamide              |
| Tread Material Mix    | Polyurethane, injected |
| Bearing               | Precision ball bearing |
| Tread Color           | Slate grey (RAL7015)   |
| Wheel Color           | Slate grey (RAL7015)   |
| Threadguards          | With threadguard       |
| Diameter              | 100 mm                 |
| Tread width           | 20 mm                  |
| Axle Hole Diameter    | 0 mm                   |
| Hub Length            | 0 mm                   |
| Body width            | 20 mm                  |
| Hardness of tread (A) | 92 Shore A             |

## FITTING

|                    |                    |
|--------------------|--------------------|
| Fitting type       | Blind hole for B10 |
| Bolt hole diameter | 11 mm              |

Deutscher  
Designer  
ClubInterzum  
Awardproduct  
design  
awardIF Design  
Award

# LINEA LIGHT




5925UAP100L51-11 7001/3000/7015

EAN 4031582350562

Order number 00770455  
Product Drawings



BETTER MOBILITY. BETTER LIFE.



Deutscher  
Designer  
Club



Interzum  
Award



product  
design  
award

IF Design  
Award