

AGILA

267FPOO3X1.25P30-13

EAN 4031582435252



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-------------------------|--|
| Product name | Agila |
| Housing type | Castor with butterfly wheel brake |
| Standard | Institute of Casters and Wheel Manufacturers |
| Load capacity at 3 km/h | 115 kg |
| Load capacity Static | 230 kg |
| Overall height | 100 mm |

WHEEL

| | |
|-----------------------|---------------------------|
| Body material | Polypropylene |
| Tread material | Identical with wheel body |
| Bearing | Plain bearing |
| Threadguards | Without threadguard |
| Diameter | 76.2 mm |
| Tread width | 31.75 mm |
| Axle hole diameter | 10 mm |
| Hardness of tread (D) | 66 Shore D |

HOUSING

| | |
|---------------------|---------------------|
| Material fork | Steel sheet, medium |
| Fork shape | Broad, reinforced |
| Swivel bearing | Two ball races |
| Offset | 36 mm |
| Swivel radius | 74.1 mm |
| Swivel interference | 148.2 mm |

FITTING

| | |
|--------------------|--|
| Fitting type | Bolt hole |
| Bolt hole diameter | 13 mm |
| Hint | Castors can be mounted with standard screws of any length. |