

PURETECH

PIR 125x37-Ø12 HL48

EAN 4031582320350



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Puretech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	100 kg
Electric Conductive	No
Stainless	No
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.47 kg

WHEEL

Body material	Polypropylene
Tread Material Mix	Solid rubber, non-marking
Bearing	Roller bearing
Wheel Color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	125 mm
Tread width	37 mm
Axle Hole Diameter	12 mm
Hub Length	48 mm
Body width	37 mm
Hardness of tread (A)	80 Shore A

PURETECH

PIR 125x37-Ø12 HL48

EAN 4031582320350

Order number 00030824

Product Drawings



BETTER MOBILITY. BETTER LIFE.

