

# KAPPA LOAD

9651FTP150P63 CL67

EAN 4031582314427  
Order number 00830281



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ● ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                                     |
|-----------------------------|-------------------------------------|
| Product name                | Kappa load                          |
| Housing type                | Swivel castor with directional lock |
| Standard                    | EN12533 - Heavy Duty Castors        |
| Load capacity at 2.5 mph    | 2116.44 lb                          |
| Load capacity at 3.7 mph    | 1763.7 lb                           |
| Load capacity Static        | 3527.39 lb                          |
| Temperature range (Minimum) | 14 °F                               |
| Temperature range (Maximum) | 140 °F                              |
| Overall height              | 7.87 in                             |
| Overall width               | 4.33 in                             |
| Overall weight              | 12.86 lb                            |

## WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Casting                |
| Tread material        | Polyurethane, casted   |
| Bearing               | Precision ball bearing |
| Axle                  | Screwed with nut       |
| Wheel color           | Honey yellow (RAL1005) |
| Threadguards          | With threadguard       |
| Diameter              | 5.91 in                |
| Tread width           | 1.97 in                |
| Body width            | 1.97 in                |
| Hardness of tread (A) | 92 Shore A             |
| Hardness of tread (D) | 42 Shore D             |

## HOUSING

|                     |                                        |
|---------------------|----------------------------------------|
| Material            | Cast iron, or iron forged, heavy       |
| Fork shape          | Broad, reinforced                      |
| Swivel bearing      | Deep-groove ball thrust roller bearing |
| Color               | Blue passivated                        |
| Offset              | 2.28 in                                |
| Swivel radius       | 5.41 in                                |
| Swivel interference | 10.83 in                               |
| Dome diameter       | 4.37 in                                |

## FITTING

|                             |                   |
|-----------------------------|-------------------|
| Fitting type                | Rectangular plate |
| Plate length                | 5.31 in           |
| Plate width                 | 4.33 in           |
| Plate hole length (Minimum) | 2.95 in           |
| Plate hole length (Maximum) | 3.15 in           |
| Plate hole width (Minimum)  | 2.95 in           |
| Plate hole width (Maximum)  | 4.13 in           |
| Plate hole diameter         | 0.43 in           |

# KAPPA LOAD

9651FTP150P63 CL67

EAN 4031582314427  
Order number 00830281



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

