

ALPHA

3477UOR200P63

EAN 4031582306194



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ● ○

CORE ATTRIBUTES

Product Name	Alpha
CO2 emission (scope 3)	11.37
Type	Swivel castor with total lock
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	350 kg
Electric Conductive	No
Stainless	No
Load capacity Static	700 kg
Temperature range (Minimum)	-25 °C
Temperature range (Maximum)	80 °C
Overall Height	240 mm
Overall width	96 mm
Overall weight	2.73 kg

HOUSING

Housing Material	Steel sheet, heavy
Fork shape	Broad
Swivel Bearing	Two ball races
Housing Color	Blue passivated
Offset	55 mm
Swivel radius	167 mm
Swivel interference	334 mm
Dome diameter	96 mm

WHEEL

Body material	Polyamide
Tread Material Mix	Identical with wheel body
Bearing	Roller bearing
Axle	Screwed with nut
Wheel Color	Natural white
Threadguards	Without threadguard
Diameter	200 mm
Tread width	50 mm
Body width	50 mm
Hardness of tread (D)	75 Shore D

FITTING

Fitting type	Medium rectangular plate
Plate length	137 mm
Plate width	105 mm
Plate hole length (Minimum)	75 mm
Plate hole length (Maximum)	80 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	105 mm
Plate hole diameter	11 mm

ALPHA

3477UOR200P63

EAN 4031582306194

Order number 00029853

Product Drawings



BETTER MOBILITY. BETTER LIFE.

