

DURATECH

UOR100x36-Ø12 HL44,4

EAN 4031582442762



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

| | |
|-----------------------|---------------------------|
| Body material | Polyamide |
| Tread material | Identical with wheel body |
| Bearing | Roller bearing |
| Threadguards | Without threadguard |
| Diameter | 3.94 in |
| Tread width | 1.42 in |
| Axle hole diameter | 0.47 in |
| Hub length | 1.75 in |
| Hardness of tread (D) | 75 Shore D |

PERFORMANCE

| | |
|----------------------|-------------|
| Roll Performance | ● ● ● ● ○ ○ |
| Movement noise | ● ● ● ● ○ ○ |
| Attrition | ● ● ● ● ● ● |
| Corrosion resistance | ● ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Duratech |
| Type | Wheel |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph | 440.92 lb |
| Electric conductive | no |
| Stainless | no |
| Load capacity Static | 881.85 lb |
| Temperature range (Minimum) | -13 °F |
| Temperature range (Maximum) | 176 °F |
| Overall weight | 0.39 lb |

DURATECH

UOR100x36-Ø12 HL44,4

EAN 4031582442762



BETTER MOBILITY. BETTER LIFE.

Product Drawings

