

ALPHA

3477UFJ125P30-13

EAN 4031582381498



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja ●●●○○

Buka u pokretu ●●●●●

Ishrana ●●●○○

otpornost na rdju ●●●○○

OSNOVNI ATRIBUTI

Naziv proizvoda	Alpha
Tip	Okreni Tocak sa potpuna kocnica
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	160 kg
Statički Nosivost	320 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	80 °C
Sveukupna visina	155 mm
Ukupna težina	1,274 kg

TOCAK

Materijal za telo	poliamid
	mekan
materijal omotaca	Elastična guma, neobeležena, vulkanizovana
Nošenje	kotrljajući lezaj
osovina	Završena sa navrtkom
štitnici omotaca	Sa threadguard
Prečnik	125 mm
Širina omotac	40 mm
Teškoća gazećeg omotac (A)	64 Šešelj A

KUCISTE

Materijal	Čelični list, težak
oblik viljuska	siroko
okretni lezaj	Dve lopte
ofset	40 mm
okretni radijus	121 mm
Otpor okretanju	242 mm

PRILAGOĐAVANJE

Tip uklapanja	otvor za vijak
dimenzija rupa sraf	13 mm

ALPHA

3477UFJ125P30-13

EAN 4031582381498



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

