

PRODUCT INFORMATION

BASETECH

POI 038x20-Ø6,1 HL21,5

EAN 4031582320695



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Basetech
Type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	35 kg
Electric Conductive	No
Stainless	No
Load capacity Static	70 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.01 kg



BETTER MOBILITY. BETTER LIFE.

WHEEL

Body material	Polypropylene
Tread Material Mix	Identical with wheel body
Bearing	Plain bearing with spacer tube
Wheel Color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	38 mm
Tread width	20 mm
Axle Hole Diameter	6 mm
Hub Length	21.5 mm
Body width	20 mm
Hardness of tread (D)	65 Shore D

BASETECH

POI 038x20-Ø6,1 HL21,5

EAN 4031582320695

Order number 00050767

Product Drawings



BETTER MOBILITY. BETTER LIFE.

