

PURETECH

PVR 300x50-Ø20 HL58

EAN 4031582321357



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja	● ● ● ● ○ ○
Buka u pokretu	● ● ● ● ○
Ishrana	● ● ● ● ○ ○
otpornost na rdju	● ● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Puretech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	250 kg
Električni provod	no
nerdjajuci	no
Statički Nosivost	500 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	2.82 kg

TOCAK

Materijal za telo	polipropilen
materijal omotaca	Cvrsta guma crna
Nošenje	kotrljajući lezaj
Boja Tocak	Grafitna crna (RAL9011)
štيتnici omotaca	Bez stražara
Prečnik	300 mm
Širina omotac	50 mm
dimenzija rupa osovina	20 mm
dužina glavnice	58 mm
Širina tela	50 mm
Teškoća gazećeg omotac (A)	80 Šešelj A

PURETECH

PVR 300x50-Ø20 HL58

EAN 4031582321357

Broj porudžbine 00038262
Product Drawings



BETTER MOBILITY. BETTER LIFE.

