

DELTA TWIN

9942ITP160P63

EAN 4031582365788



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Delta twin
Housing type	Swivel castor with total lock, head end of castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	750 kg
Load capacity at 6 km/h	600 kg
Load capacity Static	1500 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall height	210 mm
Overall width	157 mm
Overall weight	6.15 kg

WHEEL

Body material	Aluminium
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel color	Honey yellow (RAL1005)
Threadguards	Without threadguard
Diameter	160 mm
Tread width	50 mm
Body width	50 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

HOUSING

Material	Iron forged, heavy
Fork shape	Twin wheel housing
Swivel bearing	Precision ball bearing
Colour	Transparent coating
Offset	55 mm
Swivel radius	159 mm
Swivel interference	318 mm
Dome diameter	136 mm

FITTING

Fitting type	Rectangular plate
Plate length	137 mm
Plate width	105 mm
Plate hole length (Minimum)	75 mm
Plate hole length (Maximum)	80 mm
Plate hole width (Minimum)	105 mm
Plate hole width (Maximum)	105 mm
Plate hole diameter	11 mm

DELTATWIN

9942ITP160P63

EAN 4031582365788



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

