

LINEA LOW HEIGHT

5940UAP075P30-10 LH 9002/7015/9002

EAN 4031582370768



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ●
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ● ○

CORE ATTRIBUTES

Product Name	Linea low height
CO2 emission (scope 3)	1.18
Type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	90 kg
Electric Conductive	No
Stainless	No
Load capacity Static	180 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall Height	78 mm
Overall width	58 mm
Overall weight	0.21 kg

HOUSING

Housing Material	Polyamide
Fork shape	Twin wheel housing
Swivel Bearing	Precision ball bearing
Housing Color	Grey white (RAL9002)
Offset	23 mm
Swivel radius	60.5 mm
Swivel interference	121 mm
Dome diameter	30 mm

WHEEL

Body material	Polyamide
Tread Material Mix	Polyurethane, injected
Bearing	Precision ball bearing
Tread Color	Slate grey (RAL7015)
Wheel Color	Slate grey (RAL7015)
Threadguards	With threadguard
Diameter	75 mm
Tread width	15 mm
Axle Hole Diameter	0 mm
Hub Length	0 mm
Body width	15 mm
Hardness of tread (A)	92 Shore A

FITTING

Fitting type	Bolt hole
Bolt hole diameter	10 mm

LINEA LOW HEIGHT

5940UAP075P30-10 LH 9002/7015/9002

EAN 4031582370768

Order number 00770588

Product Drawings



BETTER MOBILITY. BETTER LIFE.

