

AGILA

2477PJH125P30 - 13

EAN 4031582445398



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila
Housing type	Swivel castor with total lock
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	160 mm
Overall width	60 mm
Overall weight	0.75 kg

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Threadguards	With threadguard
Diameter	125 mm
Tread width	32 mm
Hardness of tread (A)	87 Shore A

HOUSING

Material fork	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Two ball races
Offset	41 mm
Swivel radius	131 mm
Swivel interference	262 mm

FITTING

Fitting type	Bolt hole
Bolt hole diameter	13 mm
Hint	Castors can be mounted with standard screws of any length.

AGILA

2477PJH125P30 - 13

EAN 4031582445398



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

