

PRODUCT INFORMATION

ELASTECH

IEP 100X40 HL45 ASM.

EAN 4031582319668
Order number 00002341



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Aluminium
Tread material	Elastic tire, black, vulcanized
Bearing	Precision ball bearing
Wheel color	Metallic
Threadguards	Without threadguard
Diameter	100 mm
Tread width	40 mm
Axle hole diameter	8 mm
Hub length	45 mm
Body width	40 mm
Hardness of tread (A)	68 Shore A

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Elastech
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	200 kg
Load capacity Static	400 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	85 °C
Overall weight	0.51 kg

ELASTECH

IEP 100X40 HL45 ASM.

EAN 4031582319668
Order number 00002341



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

