

# E-DRIVE FLEX

EDFAUFF125P60

EAN 4031582416664  
Order number 00061635



BETTER MOBILITY. BETTER LIFE.




Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	E-Drive flex
Type	Drive Unit
Temperature range (Minimum)	5 °C
Temperature range (Maximum)	40 °C
Overall width	190 mm
Overall weight	6.52 kg
Length	Max. 315 mm (emergency release actuated)
Wheel diameter	125 mm, wear limit Ø 115 mm
Wheel tread	Solid rubber, non-marking, Shore A 63
Wheel width	35 mm
Width	190 mm
Maximum thrust force	25 N
Maximum lifting force / contact pressure force	400 N
Height in home position	140 mm
Installation height	170 mm
Emergency release	Mechanical
Protection type	IPX4 (splash water from all sides, all plugs plugged in)
Permissible ambient temperature	Operating temperature 5 °C to 40 °C, air humidity 90 %, non-condensing
Weight	6 kg
Maximum speed	4 km/h
Floor distance	30 mm
Ground unevenness (Minimum)	-15 mm
Ground unevenness (Maximum)	15 mm
Permissible storage temperature (Minimum)	-10 °C
Permissible storage temperature (Maximum)	45 °C

# E-DRIVE FLEX

EDFAUFF125P60

EAN 4031582416664  
Order number 00061635



BETTER MOBILITY. BETTER LIFE.

## WHEEL

Body material	Polyamide
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Flanged wheel
Wheel color	Silver grey (RAL7001)
Diameter	125 mm
Tread width	40 mm
Body width	40 mm
Hardness of tread (A)	63 Shore A

## HOUSING

Material fork	Electric
Fork shape	Drive
Swivel bearing	F-E-Drive ultimate
Colour	Blue passivated

## FITTING

Fitting type	Rectangular plate
Plate length	100 mm
Plate width	95 mm
Plate hole length (Maximum)	60 mm
Plate hole width (Maximum)	100 mm
Plate hole diameter	9 mm

## DRIVE UNIT TRAVEL MOTOR

Nominal voltage	24 V
Nominal current	7 Ah
Nominal output	73.1 W
Nominal speed	174.5 m/mn
Directions of travel	Forwards and backwards

## DRIVE UNIT ACTUATOR

Nominal voltage	24 V
Nominal current	3.5 Ah
Nominal output	14.8 W
Nominal speed	35.3 m/mn

# E-DRIVE FLEX

EDFAUFF125P60

EAN 4031582416664  
Order number 00061635



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

