

ELASTECH

IEP 100X40 HL45 ASM.

EAN 4031582319668
Broj porudžbine 00002341

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	Aluminijum
materijal omotaca	Elastična guma, crna, vulkanizovana
Nošenje	precizini kuglicni lezaj
Boja Tocka	Metalni
stitnici omotaca	Bez stražara
Prečnik	100 mm
Širina omotac	40 mm
dimenzija rupa osovine	8 mm
dužina glavnice	45 mm
Širina tela	40 mm
Teškoća gazećeg omotac (A)	68 Šešelj A

PERFORMANSE

Performanse kotrljanja	● ● ● ● ○
Buka u pokretu	● ● ● ● ●
Ishrana	● ● ● ○ ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Elastech
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	200 kg
Statički Nosivost	400 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	85 °C
Ukupna težina	0,51 kg

ELASTECH

IEP 100X40 HL45 ASM.

EAN 4031582319668
Broj porudžbine 00002341



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

