

# ELASTECH

IEP 100X40 HL45 ASM.

EAN 4031582319668

Broj porudžbine 00002341



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOCAK

Materijal za telo	Aluminijum
	mekan
materijal omotaca	Elastična guma, crna, vulkanizovana
Nošenje	precizini kuglični lezaj
Boja Tocak	Metalni
stićnici omotaca	Bez stražara
Prečnik	100 mm
Širina omotac	40 mm
dimenzija rupa osovina	8 mm
dužina glavčine	45 mm
Širina tela	40 mm
Teškoća gazećeg omotac (A)	68 Šešelj A

## PERFORMANSE

Performanse kotrljanja	● ● ● ● ○
Buka u pokretu	● ● ● ● ●
Ishrana	● ● ● ○ ○
otpornost na rdju	● ● ● ○ ○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Elastech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	200 kg
Statički Nosivost	400 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	85 °C
Ukupna težina	0,51 kg

# ELASTECH

IEP 100X40 HL45 ASM.

EAN 4031582319668  
Broj porudžbine 00002341



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

