

R47-32-36 INOX

EAN 4031582428322



Image may differ from the original product

PERFORMANCE

Corrosion resistance ● ● ● ○ ○

CORE ATTRIBUTES

|                             |           |
|-----------------------------|-----------|
| Product name                | Accessory |
| Housing type                | Accessory |
| Temperature range (Minimum) | -10 °C    |
| Temperature range (Maximum) | 40 °C     |
| Overall weight              | 0.167 kg  |

FITTING

|                            |                                                            |
|----------------------------|------------------------------------------------------------|
| Fitting type               | Synthetic expander, square                                 |
| Expander fitting (Minimum) | 32 mm                                                      |
| Expander fitting (Maximum) | 36 mm                                                      |
| Hint                       | Please indicate required tube innerdiameter when ordering. |