

# ELASTECH

IEP 250X50-Ø20 HL60

EAN 4031582319750  
Order number 00801772



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Aluminium
Tread hardness	soft
Tread material	Elastic tire, black, vulcanized
Bearing	Precision ball bearing
Wheel color	Jet black (similar RAL9005)
Threadguards	Without threadguard
Diameter	250 mm
Tread width	50 mm
Axle hole diameter	20 mm
Hub length	60 mm
Body width	50 mm
Hardness of tread (A)	68 Shore A

## PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ● ● ●
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ●

## CORE ATTRIBUTES

Product name	Elastech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	500 kg
Load capacity at 6 km/h	400 kg
Load capacity Static	1000 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	85 °C
Overall weight	2.37 kg

# ELASTECH

IEP 250X50-Ø20 HL60

EAN 4031582319750  
Order number 00801772



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

