

AGILA

2470UOO050P40

EAN 4031582301281
Order number 00004988



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila
Type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	110.23 lb
Load capacity Static	220.46 lb
Temperature range (Minimum)	-13 °F
Temperature range (Maximum)	176 °F
Overall height	2.72 in
Overall width	1.69 in
Overall weight	0.39 lb

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Plain bearing
Wheel color	Slate gray (RAL7015)
Threadguards	Without threadguard
Diameter	1.97 in
Tread width	0.79 in
Body width	0.79 in
Hardness of tread (D)	75 Shore D

HOUSING

Material	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Two ball races
Color	Blue passivated
Offset	0.94 in
Swivel radius	1.93 in
Swivel interference	3.86 in
Dome diameter	1.61 in

FITTING

Fitting type	Square plate
Plate length	2.36 in
Plate width	2.36 in
Plate hole length (Minimum)	1.5 in
Plate hole length (Maximum)	1.89 in
Plate hole width (Minimum)	1.5 in
Plate hole width (Maximum)	1.89 in
Plate hole diameter	0.25 in

AGILA

2470UOO050P40

EAN 4031582301281
Order number 00004988



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

