

## LINEA

5941UAP125P30-13 RAL9002

EAN 4031582369236



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## PERFORMANSE

Performanse kotrljanja ●●●●●

Buka u pokretu ●●●○○

Ishrana ●●●●○

otpornost na rdju ●●●●○

## OSNOVNI ATRIBUTI

|                                |                                  |
|--------------------------------|----------------------------------|
| Naziv proizvoda                | Linea                            |
| Tip                            | Okreni Tocak sa usmerena kocnica |
| Standard                       | EN12530 - Kastori uređaja        |
| Nosivost na 3 km/h             | 130 kg                           |
| Statički Nosivost              | 260 kg                           |
| Temperaturni opseg (Minimalno) | -10 °C                           |
| Opseg temperature (maksimalni) | 40 °C                            |
| Sveukupna visina               | 143 mm                           |
| Ukupna širina                  | 82 mm                            |
| Ukupna težina                  | 0,873 kg                         |

## TOCAK

|                            |                          |
|----------------------------|--------------------------|
| Materijal za telo          | poliamid                 |
| materijal omotaca          | Poliuretan, liveno       |
| Nošenje                    | precizini kuglicni lezaj |
| štitnici omotaca           | Sa threadguard           |
| Prečnik                    | 125 mm                   |
| Širina omotac              | 20 mm                    |
| Teškoća gazećeg omotac (A) | 92 Šor A                 |

## KUCISTE

|                 |                          |
|-----------------|--------------------------|
| Materijal       | poliamid                 |
| oblik viljuska  | kuciste za dva Tocak     |
| okretni lezaj   | precizini kuglicni lezaj |
| Boja            | Siva bela (RAL9002)      |
| ofset           | 40 mm                    |
| okretni radijus | 129 mm                   |
| Otpor okretanju | 258 mm                   |
| Prečnik kupole  | 52 mm                    |

## PRILAGOĐAVANJE

|                     |                |
|---------------------|----------------|
| Tip uklapanja       | otvor za vijak |
| dimenzija rupa sraf | 13 mm          |

Deutscher  
dizajner  
ClubInterzum  
nagradaIF nagrada za  
Dizajn

## TEHNIČKI CRTEŽI

