

# ALPHA

3470PXU160P63

EAN 4031582304848



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ○ ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Alpha                         |
| Housing type                | Swivel castor                 |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 4 km/h     | 135 kg                        |
| Load capacity Static        | 270 kg                        |
| Temperature range (Minimum) | -20 °C                        |
| Temperature range (Maximum) | 60 °C                         |
| Overall height              | 200 mm                        |
| Overall weight              | 2.043 kg                      |

## WHEEL

|                       |   |
|-----------------------|---|
| Body material         | Polypropylene   |
| Tread material        | Polyurethane, biosourced, injected, electric-conductive |
| Bearing               | Plain bearing with synthetic spacer Tube                |
| Axle                  | Screwed with nut  |
| Diameter              | 160 mm  |
| Tread width           | 40 mm   |
| Hardness of tread (A) | 85 Shore A  |

## HOUSING

|                     |                    |
|---------------------|--------------------|
| Material fork       | Steel sheet, heavy |
| Fork shape          | Broad              |
| Swivel bearing      | Two ball races     |
| Offset              | 55 mm              |
| Swivel radius       | 135 mm             |
| Swivel interference | 270 mm             |

## FITTING

|                             |                   |
|-----------------------------|-------------------|
| Fitting type                | Rectangular plate |
| Plate length                | 137 mm            |
| Plate width                 | 105 mm            |
| Plate hole length (Maximum) | 105 mm            |
| Plate hole width (Minimum)  | 75 mm             |
| Plate hole width (Maximum)  | 80 mm             |
| Plate hole diameter         | 11 mm             |

# ALPHA

3470PXU160P63

EAN 4031582304848



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

