

ELASTECH

IEP 200X50-Ø25 HL60

EAN 4031582319743

Broj porudžbine 00804060



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	Aluminijum
	mekan
materijal omotaca	Elastična guma, crna, vulkanizovana
Nošenje	precizini kuglični lezaj
Boja Tocak	Crni mlaz (sličan RAL9005)
štitnici omotaca	Bez stražara
Prečnik	200 mm
Širina omotac	50 mm
dimenzija rupa osovina	25 mm
dužina glavčine	60 mm
Širina tela	50 mm
Teškoća gazećeg omotac (A)	68 Šešelj A

PERFORMANSE

Performanse kotrljanja ● ● ● ● ●

Buka u pokretu ● ● ● ● ●

Ishrana ● ● ● ● ●

otpornost na rdju ● ● ● ● ●

OSNOVNI ATRIBUTI

Naziv proizvoda	Elastech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	450 kg
Nosivost na 6 km/h	360 kg
Statički Nosivost	900 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	85 °C
Ukupna težina	1,709 kg

ELASTECH

IEP 200X50-Ø25 HL60

EAN 4031582319743
Broj porudžbine 00804060



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

