

# KAPPA LOAD

9658FCP160P63

EAN 4031582451924



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ● ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                              |
|-----------------------------|------------------------------|
| Product name                | Kappa load                   |
| Housing type                | Fixed castor                 |
| Standard                    | EN12533 - Heavy Duty Castors |
| Load capacity at 4 km/h     | 900 kg                       |
| Load capacity at 6 km/h     | 750 kg                       |
| Load capacity Static        | 1800 kg                      |
| Temperature range (Minimum) | -20 °C                       |
| Temperature range (Maximum) | 60 °C                        |
| Overall height              | 205 mm                       |
| Overall weight              | 3.693 kg                     |

## WHEEL

|                |                                |
|----------------|--------------------------------|
| Body material  | Casting                        |
| Tread material | Ultratech Polyurethane, casted |
| Bearing        | Precision ball bearing         |
| Axle           | Screwed with nut               |
| Threadguards   | With threadguard               |
| Diameter       | 160 mm                         |
| Tread width    | 50 mm                          |

## HOUSING

|               |                    |
|---------------|--------------------|
| Material fork | Iron forged, heavy |
| Fork shape    | Broad, reinforced  |

## FITTING

|                             |                   |
|-----------------------------|-------------------|
| Fitting type                | Rectangular plate |
| Plate length                | 135 mm            |
| Plate width                 | 110 mm            |
| Plate hole length (Maximum) | 105 mm            |
| Plate hole width (Minimum)  | 75 mm             |
| Plate hole width (Maximum)  | 80 mm             |
| Plate hole diameter         | 11 mm             |

# KAPPA LOAD

9658FCP160P63

EAN 4031582451924



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

